



What is it and what does it do?

The Dual Straw Insert offers both a dual flow rate and dual dilution from a single insert.

The two separate flow channels enable the end-user to pull two separate dilutions from the same chemical bottle into either a wall dispenser or a PDU from a single insert.

This is great for environments where you require different dilutions of the same chemical for different uses e.g. filling a trigger bottle for a window cleaning solution and a mop bucket for cleaning floors.

To establish chemical flow, the end user replaces the ship cap with a SaFTFlo® Cap Adapter which opens the insert valve, releasing chemical. A fully closed-loop system ensures that end users are never exposed directly to chemical concentrates.

Benefits


- A dual flow rate from a single insert
- Dual dilution in a single insert
- Can pull the correct dilution for a small trigger bottle and a mop bucket from the same chemical bottle without change over
- Provides a closed-loop system

Key Features

- Available in 38mm standard flow rate
- Enables end user to pull two different dilutions from the same bottle of chemical
- Designed to work with the Dual Flow Portable Dispensing Unit and Dual Port Cap Adapter.
- 32 metering options
- Materials:
 - » Plug: Polypropylene / HDPE
 - » Venting: PE Foam Liner
 - » Spring: Hastelloy, Stainless Steel, TPE
- Colors: please contact your sales representative
- Key lock options available for additional seal and security

Compatible Products

- Dual Flow Portable Dispenser



Industries Used In



Patent Number: 10,625,911